

# Transepitelial Multi-Use®



## Hexàgon Extern



### Pilars Multi-Use®

#### Pilar Recte Multi-Use® (Titani Grau 5)

30 Ncm (max.)					
	<b>h1.0 mm</b>	<b>h2.0 mm</b>	<b>h3.0 mm</b>	<b>h4.0 mm</b>	<b>h5.0 mm</b>
	NP VEXT10N1000	VEXT10N2000	VEXT10N3000	-	-
	RP VEXT10R1000	VEXT10R2000	VEXT10R3000	VEXT10R4000	VEXT10R5000

#### Pilar Angulat Multi-Use® (Titani Grau 5)

30 Ncm (max.)						
	<b>17° h2.0 mm</b>	<b>17° h3.0 mm</b>	<b>17° h4.0 mm</b>	<b>30° h3.0 mm</b>	<b>30° h4.0 mm</b>	<b>30° h5.0 mm</b>
	NP -	-	-	-	-	-
	RP VEXT10R2017	VEXT10R3017	VEXT10R4017	VEXT10R3030	VEXT10R4030	VEXT10R5030

### Cicatrització

#### Tap de Cicatrització Multi-Use®



(Cargol integrat)

**Titani**  
MU012

### Impressió

#### Coping d'Impressió Multi-Use® (Titani Grau 5)



**Cubeta Oberta**  
MU021



**Cubeta Tancada**  
MU022

#### Rèplica Multi-Use® (Acer Inoxidable)



MU03

## Pròtesi cargolada

Calcinable  
Multi-Use® (POM C)

Pilar de Sobrecolat  
Multi-Use® (CrCo + POM C)

Pilar Provisional  
Multi-Use®



MU0402



MU0502



Titanio  
MU0602



PEEK  
MU0602P

## Cargol Protèsic Multi-Use® (Titani Grau 5)

15 Ncm (max.)



Titani DLC  
MU0905T



Titani  
MU0905

## Pilar Sobrecolat Angulat Multi-Use®



Antirrotatori - 17°  
1- VCHA170001  
2- MU0504



Antirrotatori - 30°  
1- VCHA300001  
2- MU0504

## Cargol Protèsic Multi-Use® Angulat

Connexió Tetralobular

15 Ncm (max.)



Titani  
MU0900-TLB



Curta  
VSDTLB-1

Mitja  
VSDTLB-2

Llarga  
VSDTLB-3

## Clau Recta Multi-Use®



Contra-Àngle  
VDMU-1



Carraca  
VDMU-2



Transportador  
Multi-Use® Recte  
VDMU-4

